


# TOSHIBA

## Fast Medium Wave Infrared Emitter for Bodycare



# Zenit



**TOSHIBA ZENIT** heat emitter is designed for body relaxation applications such as Infrared cabin.

Thanks to **TOSHIBA** Infrared technology, fast start will save warm-up time, a compact design will allow installation in narrow spaces, with optimum proportion of infrared spectrum for a totally safe use.

With **TOSHIBA ZENIT** heat emitter, more uniform and relaxing heat can be enjoyed for a perfect wellness.



### Avantages :



- › Optimum proportion of infrared heat
- › Fast start without warm up time, energy saving
- › Compact and easy to install
- › Healthy and comfortable heat

**Toshiba Lighting Products (France) S.A.**

42 Rue St Dizier, 54000 Nancy Phone : + 33 (0) 3 83 39 00 83 [www.toshiba-lighting.com](http://www.toshiba-lighting.com)




# Zenit




Non-exhaustive list, for reference only. Possibility of customization.

Designation	Watts (W)	Volts (V)	Wire length WL1 (mm)	Wire length WL2 (mm)	Connection / Terminal end	Overall length OAL (mm)	Heating length CL (mm)	Burning position	Ave. Life (hrs)	Order number	Technical drawing
JHT 235V 350W 550 BfU	350	235	300 ± 10	1590 ± 25	Splice	626 ± 2	550	Universal	5000	4JHS170	EM-907
JHT 235V 500W 550 BfU	500	235	300 ± 10	1590 ± 25	Splice	626 ± 2	550	Universal	5000	TBA	EM-1555
JHT 235V 500W 700 BfU	500	235	300 ± 10	1590 ± 25	Splice	785 ± 2	700	Universal	5000	4JHS025	EM-905
JHT 235V 750W 700 BfU	750	235	300 ± 10	1590 ± 25	Splice	785 ± 2	700	Universal	5000	4JHS169	EM-906

Cables terminal can be modified on request (*Faston, fork, end striped, ring...*) – For other power or dimension please contact us.



TOSHIBA ZENIT Emitter IR heat proportion (internal comparison)



## Toshiba Lighting Products (France) S.A.

42 Rue St Dizier, 54000 Nancy Phone : + 33 (0) 3 83 39 00 83 www.toshiba-lighting.com